


NK80B



● Order No. Example

NK80B 20



Ground Specification



Welded Specification

- ChainNo.80
- Chain Pitch(P)25.4mm
- Roller Link Inner Width(W)15.88mm
- Roller Outside Diameter(Dr)15.88mm
- Tooth Width(T)14.6 mm

Type	No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Shaft Hole Diameter d			Boss Diameter BD	Boss Length BL	Shape	Material	Weight kg	¥	Semi-F ¥	
				Prepared Hole Product	Minimum	Maximum								
NK80B	8	77	66.37	14	15	22	★49	40	Ground Specification	High-frequency Hardened Teeth	0.70			
	9	85	74.27	14	15	35	★58	40			0.87			
	10	93	82.19	15	16	32	52	40			1.02			
	11	102	90.16	15	16	38	60	40			1.25			
	12	110	98.14	15	16	45	67	40			1.60			
	13	118	106.14	16	17	51	77	40			1.90			
	14	127	114.15	16	17	51	77	40		2.15				
	15	135	122.17	20	21	63	93	40		2.30				
	16	143	130.20	20	21	63	93	40		2.50				
	17	151	138.23	20	21	63	93	40		2.95				
	18	159	146.27	20	21	63	93	40		3.15				
	19	167	154.32	20	21	63	93	40		3.40				
	20	176	162.37	20	21	63	93	40		3.60				
	21	184	170.42	20	21	63	93	40		3.85				
	22	192	178.48	26	27	75	107	45		Ground Specification	Common Steel	5.00		
	23	200	186.54	26	27	75	107	45				5.23		
	24	208	194.60	26	27	75	107	45				5.50		
	25	216	202.66	26	27	75	107	45	5.80					
	26	224	210.72	26	27	75	107	45	6.10					
	27	233	218.79	26	27	75	107	45	6.40					
	28	241	226.86	26	27	75	107	45	6.75					
	29	249	234.93	26	27	75	107	45	7.10					
	30	257	243.00	26	27	75	107	45	7.40					
	31	265	251.07	26	27	75	107	45	7.80					
	32	273	259.14	26	27	75	107	45	8.15					
	33	281	267.21	26	27	75	107	45	8.50					
	34	289	275.29	26	27	75	107	45	8.90					
	35	297	283.36	26	27	75	107	45	9.30					